


product data sheet

item no. 92.034.0458.0

device connector GST18I3L S1H PB04

gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model male, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier pastel blue



item no.	92.034.0458.0
EAN	4015573682245
order unit	100 piece(s)

certificates / approvals



technical data

general

rated current	20 A
rated voltage	250 V
pollution degree	2
mechanical coding	code 5
rated impulse voltage	4 kV
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	pastel blue
Pole codification	1, 2, 3

connection data

terminations per pole	1
-----------------------	---

model

model	male
connection type	soldering connection
angle of plug	square
inclination	90 °
degree of protection (IP)	IP20
built-in component	soldering connection

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.026 kWh/St
insulation components continuous temperature	100 °C
surface finish	tin-plated

dimensions

length	24 mm
--------	-------

width	28.2 mm
height	13 mm

