

Crimpzange / Crimp tool 95.101.0800.0

Bestellnummer Order-no.		Kontakt- Ø Contact- Ø	Anschluss-Ø Cross section		Oberfläche Surface	Abisolierlänge (mm) Stripping length	Crimpbacken Crimping jaws	Nr. No.:	VPE	Kontaktaufnahme Contact guide	Verwendung Usage			Lösewerkzeug Release tool
Buchse female	Stecker male plug	mm	mm²	AWG							PST40 FA / GA	PST40 FA (Feldanschluss) (fieldwiring)	PST40 GA (Geräteanschluss) (pulkhead connector)	
02.125.8000.8	05.545.2000.8	4	1,5	-	Ag	17	B	05.502.2100.0	50	05.502.3700.0	x			05.502.1600.0
02.125.8002.8	05.545.2002.8	4	1,5	-	Ag	17	B	05.502.2100.0	100	05.502.3700.0	x			05.502.1600.0
99.200.0000.7	99.205.0000.7	4	1,5	-	Ag	17	B	05.502.2100.0	100	05.502.3700.0		x		05.502.1600.0
99.220.0000.7	99.225.0000.7	4	1,5	-	Ag	17	B	05.502.2100.0	100	05.502.3700.0			x	05.502.1600.0
02.125.8100.8	05.545.2100.8	4	2,5	-	Ag	17	B	05.502.2100.0	50	05.502.3700.0	x			05.502.1600.0
02.125.8102.8	05.545.2102.8	4	2,5	-	Ag	17	B	05.502.2100.0	100	05.502.3700.0	x			05.502.1600.0
99.201.0000.7	99.206.0000.7	4	2,5	-	Ag	17	B	05.502.2100.0	100	05.502.3700.0		x		05.502.1600.0
99.221.0000.7	99.226.0000.7	4	2,5	-	Ag	17	B	05.502.2100.0	100	05.502.3700.0			x	05.502.1600.0
02.125.8200.8	05.545.2200.8	4	4,0	-	Ag	17	D	05.502.2300.0	50	05.502.3700.0	x			05.502.1600.0
02.125.8202.8	05.545.2202.8	4	4,0	-	Ag	17	D	05.502.2300.0	100	05.502.3700.0	x			05.502.1600.0
99.202.0000.7	99.207.0000.7	4	4,0	-	Ag	17	D	05.502.2300.0	100	05.502.3700.0		x		05.502.1600.0
99.222.0000.7	99.207.0000.7	4	4,0	-	Ag	17	D	05.502.2300.0	100	05.502.3700.0			x	05.502.1600.0
02.125.8300.8	05.545.2300.8	4	6,0	-	Ag	17	D	05.502.2300.0	50	05.502.3700.0	x			05.502.1600.0
02.125.8302.8	05.545.2302.8	4	6,0	-	Ag	17	D	05.502.2300.0	100	05.502.3700.0	x			05.502.1600.0
99.203.0000.7	99.208.0000.7	4	6,0	-	Ag	17	D	05.502.2300.0	100	05.502.3700.0		x		05.502.1600.0
99.223.0000.7	99.228.0000.7	4	6,0	-	Ag	17	D	05.502.2300.0	100	05.502.3700.0			x	05.502.1600.0
02.125.8400.8	05.545.2400.8	4	10,0	-	Ag	17	D	05.502.2300.0	50	05.502.3700.0	x			05.502.1600.0
02.125.8402.8	05.545.2402.8	4	10,0	-	Ag	17	D	05.502.2300.0	100	05.502.3700.0	x			05.502.1600.0
99.202.0000.7	99.209.0000.7	4	10,0	-	Ag	17	D	05.502.2300.0	100	05.502.3700.0		x		05.502.1600.0
99.224.0000.7	99.229.0000.7	4	10,0	-	Ag	17	D	05.502.2300.0	100	05.502.3700.0			x	05.502.1600.0

Legende / Legend

- **Blaue Kennzeichnung:** Komplettes Bauteil (Kontakte mit jeweiligem Gehäuse)
- **Blue marking:** Complete component (contacts and respective housing)