

Product data sheet

Item No. 07.416.6453.0

Reducer plate 24/10

revos reducer plate size 24/size 10



Item No.	07.416.6453.0
EAN	4015573429970
Order Unit	10 Piece(s)

Certificates / Approvals

Technical data

General

Construction	24
Length	150 mm
Width	52 mm
Number of openings	1
Degree of protection (IP)	IP65
Material	Plastic
Inflammability class of insulation material acc. with UL94	V0
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C