

product data sheet

item no. 73.115.4053.0

multipole adapter HD SAS WR 40 2,5 25

Multipole adapter revos HD 250V/10A 40 pole + ground, male insert, ground right

item no.	73.115.4053.0
EAN	4015573229372
order unit	4 piece(s)

certificates / approvals



technical data

general

model	pin insert
size (in accordance with DIN 43880)	16
inflammability class of insulation material acc. with UL94	V2
color	grey
pollution degree	3
operating temperature range min.	-40 °C
operating temperature range max.	120 °C
suitable for modular version	no

connection data

connection type	screw connection
number of poles	40
plus switching contacts	0
number of pole for rated current 2	0
number of pole for rated current 3	0
total number of poles (without ground contact)	40
with wire protection	yes
Leiterquerschnitt starr (ein-/mehrdrahtig) Min.	0.5 mm²
Leiterquerschnitt starr (ein-/mehrdrahtig) Max.	2.5 mm²
protective contact	yes

technical data UL/CSA

nominal voltage according to UL/CSA	600 V
nominal current according CSA	10 A
min. conductor cross section flexible wire	0.5 mm²
max. conductor cross section flexible wire	2.5 mm²
conductor cross section flexible AWG wire	22-14 AWG

model

with housing	no
position of protective conductor	right

contacts

contact material	copper alloy
surface	tin-plated
wire strip length	12 mm
contact resistance	≤ 6 mOhm

screws head design/recomm. Torque

mounting screws	H1/0.5-0.7 Nm
clamping screws	M2.5/0.4-0.6 Nm Slot
ground conductor screws	H1/1.2-1.6 Nm


technical data DIN EN 61984

nominal voltage	250 V
nominal voltage face/ground	250 V
nominal current	10 A
rated impulse voltage	4 kV



assembly

item no.	type	description
76.326.4028.0	bottom BAS GUT GV 16H A	Bottom-base revos basic made of aluminum, with single locking lever for terminal adapters mounted on the rear, open, high version, 16-poles
76.327.4028.0	bottom BAS GUT GW 16H A	Bottom-base revos basic made of aluminum, with single locking lever and protective cover for terminal adapters mounted on the rear, open, high version, 16-poles
73.326.4028.0	bottom BAS GUT GX 16H A	Bottom-base revos basic made of aluminum, with double locking lever for terminal adapters mounted on the rear, open, high version, 16-poles
73.327.4028.0	bottom BAS GUT GY 16H A	Bottom-base revos basic made of aluminum, with double locking lever and protective cover for terminal adapters mounted on the rear, open, high version, 16-poles

Gezeichnete Ausführung
40-polig
Drawn version 40 poles



Ansicht ohne Abschlussplatte
und Schutzleiterwinkel gezeichnet!
View drawn without closing plate
and protective wire angel.



Teilenummer part number	Polzahl pole	A	B
73.115.4053.0	40	77,5	53,8
73.115.6453.0	64	104	84,3

Freitoleranz nach DIN -			CAD - Zeichnung, keine manuellen Änderungen			1.Verwendung: -		Bl.: 1 von 1						
	/	Maßstab	Werkstoff und Oberfläche:			2005		Tag	Name	T	Zeichnung Nr.		Index	
	/	1:1				Entworfen		22.02.	Schmitt J.		73.115.4053.0 01K			
	/					Geprüft		-	-					
	/					Normgepr.		-	-		Ersatz für: -			
	/													
	/		 wieland Elektrische Verbindungen					Benennung		KLEMMEN_ADAPTER mit Steckereinsatz, SL rechts Terminal adaptor plug insert earth right				
	/													
	/													
Buchstabe	Datum / Blatt													
Änderung														

Weitergabe sowie Vervielfältigung dieser Dokumente, Vervielfältigung und Verbreitung
sowie Inhalt sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the
communication of its contents to others without express authorization is prohibited.