

product data sheet

item no. 70.343.2435.0

bottom BAS GUT GI 24 M25 A0

Bottom-base revos basic made of aluminum, with double locking lever and cable gland M25 on the bottom, with protective cover (IP54), low version, 24-polig



item no.	70.343.2435.0
EAN	4015573618299
order unit	1 piece(s)

certificates / approvals



technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	24
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	below
type of cable	gland nut
with cable screw gland	yes
thread size M	25
thread size PG	
hinged lid	yes
EMC-version	no
length	144 mm
width	57 mm
height	57 mm

