

product data sheet

item no. 76.345.6435.0

bottom BAS GUT GS 24HM32 50 A0

Bottom-base revos basic made of aluminum, with single locking lever and cable gland M32 on the left side, with protective cover (IP54), low version, 24-polig



item no.	76.345.6435.0
EAN	4015573630109
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	24H
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	sideways
type of cable	gland nut
with cable screw gland	yes
thread size M	32
thread size PG	
hinged lid	yes
EMC-version	no
length	144 mm
width	57 mm
height	98 mm