

## product data sheet

item no. 71.333.2435.1

### bottom BAS GUT GO 24 M25 A1

Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the bottom, low version, 24-polig



|            |               |
|------------|---------------|
| item no.   | 71.333.2435.1 |
| EAN        | 4015573621916 |
| order unit | 1 piece(s)    |

### certificates / approvals



### technical data

#### general

|                                                          |                     |
|----------------------------------------------------------|---------------------|
| housing material                                         | aluminum            |
| color                                                    | grey                |
| surface                                                  | with powder coating |
| degree of protection (IP)                                | other               |
| UV resistant                                             | yes                 |
| flammability class of insulation material acc. with UL94 | other               |
| operating temperature range min.                         | -40 °C              |
| operating temperature range max.                         | 120 °C              |

#### model

|                        |                         |
|------------------------|-------------------------|
| construction           | 24                      |
| model of the housing   | surface mounting (base) |
| locking mechanism      | single locking lever    |
| cable entry            | below                   |
| type of cable          | thread                  |
| with cable screw gland | no                      |
| thread size M          | 25                      |
| thread size PG         |                         |
| hinged lid             | no                      |
| EMC-version            | no                      |
| length                 | 144 mm                  |
| width                  | 57 mm                   |
| height                 | 57 mm                   |

