

product data sheet

item no. 76.354.6435.0

hood BAS GOT GI 24HM32 50 A0

Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the top (IP54), low version, 24-poles



item no.	76.354.6435.0
EAN	4015573642065
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	24H
model of the housing	male
locking mechanism	single locking lever
cable entry	above
type of cable	gland nut
with cable screw gland	yes
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	120 mm
width	43 mm
height	76 mm

