

product data sheet

item no. 71.354.2435.1

hood BAS GOT GI 24 M32 A1

Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the top, low version, 24-poles



item no.	71.354.2435.1
EAN	4015573651791
order unit	1 piece(s)

certificates / approvals



technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	24
model of the housing	male
locking mechanism	single locking lever
cable entry	above
type of cable	thread
with cable screw gland	no
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	136 mm
width	43 mm
height	70 mm

