

product data sheet

item no. 73.344.4035.1

bottom BAS GUT GF 16HM32 50 A1

Bottom-base revos basic made of aluminum, for double locking lever with threaded hole M32 on the left and right side, with protective cover, high version, 16-polig



item no.	73.344.4035.1
EAN	4015573627796
order unit	1 piece(s)

certificates / approvals


technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP65
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	16H
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	two-sided
type of cable	thread
with cable screw gland	no
thread size M	32
thread size PG	
hinged lid	yes
EMC-version	no
length	117 mm
width	57 mm
height	98 mm



73.34 ₀ .4035.1	BAS GUT GF 16H ^{M32} _{M25} A1	Gewindebohrung /Thread hole	X
73.34 ₀ .4035.0	BAS GUT GF 16H ^{M32} _{M25} A0	Kabelverschraubung(KV), IP54 /Cable gland(ICG), IP54	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	der- gestellt /drawn
Weitere Daten siehe KATALOG oder eCatalog. Additional data see CATALOG or eCatalog.		www.wieland-electric.com eshop.wieland-electric.com	

Tolerierung Size ISO 14005(®)/Tolerance system Size ISO 14005(®) (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).				ja/yes ☒ Stoffverbots- und Deklarationsliste nach WH 5020.010 ist einzuhalten. Conformity with Wieland document WH 5020.010 e (list of prohibited / declaimable hazardous substances) to be declared!					
Freitoleranz nach General tolerance		DIN ISO 2768 - m		CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed		1. Verwendung: - First Use:		Blatt: 1 von 1 Sheet: 1 of 1	
/		Werkstoff/Material		2014		Tag/Date		Name	
/		Aluminium		gezeichnet drawn		21.08.		Ireschan	
/ Maßstab/Scale		beschichtet/ coated		geprüft checked		- -		- -	
/ 1:2		grau/ grey		normer- Stand, check		- -		- -	
Maße in mm/Dimensions are in mm									
/ Vol.		mm		Of L./Surf.		mm		Ersatz für/Replacement for: -	
/									
/									
Index		Datum / Blatt Date / Sheet		Type		Benennung/Title			
Änderung/Revision		www.wieland-electric.com		revos BASIC		GEHAEUSEUNTERTEIL Baugröße 16H-Kabelabgang 2x M25/M32 housing size 16H-cable outlet 2x M25/M32			