

## product data sheet

item no. 73.359.4035.2

hood BAS GOT GF 16HM32 50 A2

Hood revos basic made of aluminum, with double locking lever and nozzleM32 on the top, low version, 16-poles

|            |               |
|------------|---------------|
| item no.   | 73.359.4035.2 |
| EAN        | 4015573663688 |
| order unit | 1 piece(s)    |

## certificates / approvals

## technical data

### general

|                                                          |                     |
|----------------------------------------------------------|---------------------|
| housing material                                         | aluminum            |
| color                                                    | grey                |
| surface                                                  | with powder coating |
| degree of protection (IP)                                | other               |
| UV resistant                                             | yes                 |
| flammability class of insulation material acc. with UL94 | other               |
| operating temperature range min.                         | -40 °C              |
| operating temperature range max.                         | 120 °C              |

### model

|                        |                       |
|------------------------|-----------------------|
| construction           | 16H                   |
| model of the housing   | male                  |
| locking mechanism      | double locking levers |
| cable entry            | above                 |
| type of cable          | intermediate support  |
| with cable screw gland | no                    |
| thread size M          | 32                    |
| thread size PG         |                       |
| hinged lid             | no                    |
| EMC-version            | no                    |
| length                 | 94 mm                 |
| width                  | 56 mm                 |
| height                 | 76 mm                 |

