

product data sheet

item no. 70.355.1635.2

hood BAS GOT GD 16 M25 A2

Hood revos basic made of aluminum, with double locking lever and nozzleM25 on the right side, low version, 16-poles

item no.	70.355.1635.2
EAN	4015573606142
order unit	1 piece(s)

certificates / approvals



technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	16
model of the housing	male
locking mechanism	double locking levers
cable entry	sideways
type of cable	intermediate support
with cable screw gland	no
thread size M	25
thread size PG	
hinged lid	no
EMC-version	no
length	94 mm
width	56 mm
height	60 mm

