

product data sheet

item no. 76.353.4035.0

hood BAS GOT GG 40HM32 50 A0

Hood revos basic made of aluminum, for single locking lever with cable gland M32 on the right side (IP54), high version, size 16H



item no.	76.353.4035.0
EAN	4015573625006
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	16H
model of the housing	male
locking mechanism	single locking lever
cable entry	sideways
type of cable	gland nut
with cable screw gland	yes
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	94 mm
width	43 mm
height	76 mm

