


product data sheet

item no. 73.331.1035.0

bottom BAS GUT GC 10HM25 50 A0

Bottom-base revos basic made of aluminum, with double locking lever or screw cap with cable gland M25 on the left side (IP54), low version, 10-polig



item no.	73.331.1035.0
EAN	4015573796652
order unit	1 piece(s)

certificates / approvals

technical data

general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model



construction	10H
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	sideways
type of cable	gland nut
with cable screw gland	yes
thread size M	25
thread size PG	
hinged lid	no
EMC-version	no
length	97 mm
width	58 mm
height	67 mm

Ausführung .1
version .1


Gewinde M25
thread M25



Verschraubung M25
screw connection M25



Gezeichnete Ausführung .0 / version .0



weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-nr.	Typ type
73.331.1035.0	BAS GUT GC 10HM25 50 A0
73.331.1035.1	BAS GUT GC 10HM25 50 A1

Freitoleranz nach DIN -			CAD - Zeichnung, keine manuellen Änderungen			1.Verwendung: -		Bl.: 1 von 1	
	/	Maßstab	Werkstoff und Oberfläche:	2004	Tag	Name	T	Zeichnung Nr.	Index
	/	x		Entworfen	16.09.	Dütsch T.			
	/			Gepfält	-	-			
	/			Normgepr.	-	-			
	/	 wieland	Elektrische Verbindungen	Ersatz für: -					
	/			Benennung GEHAEUSEUNTERTEIL HOUSING LOWER PART Größe 10 / size 10 1x M25 links/left					
	/								
Buchstabe	Datum / Blatt								
Änderung									