


product data sheet

item no. 73.330.1035.0

bottom BAS GUT GB 10HM25 50 A0

Bottom-base revos basic made of aluminum, with double locking lever or screw cap with cable gland M25 on the right and left side (IP54), low version, 10-polig



item no.	73.330.1035.0
EAN	4015573758025
order unit	1 piece(s)

certificates / approvals

technical data


general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C



model

construction	10H
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	two-sided
type of cable	gland nut
with cable screw gland	yes
thread size M	25
thread size PG	
hinged lid	no
EMC-version	no
length	97 mm
width	58 mm
height	72 mm


Ausführung .1
version .1



Verschraubung M25
screw connection M25



Gezeichnete Ausführung .0 / version .0



weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-no.	Typ type
73.330.1035.0	BAS GUT GB 10HM25 50 A0
73.330.1035.1	BAS GUT GB 10HM25 50 A1

Freitoleranz nach DIN -			CAD - Zeichnung, keine manuellen Änderungen			1.Verwendung: -		Bl.: 1 von 1		
	/	Maßstab	Werkstoff und Oberfläche:		2004	Tag	Name	T	Zeichnung Nr. 73.330.1035.0 01K	Index a
	/	%			Entworfen	13.08.	Kurz H.			
	/				Geprüft	-	-			
	/				Normgepr.	-	-			
	/	 wieland	Elektrische Verbindungen		Ersatz für: -					
a	09.06.2005/				Benennung				GEHAEUSEUNTERTEIL housing lower part Größe/size 10 2x M25	
Buchstabe	Datum / Blatt									
Änderung										

Weitergabe sowie Vervielfältigung dieser Zeichnung, Vervielfältigung und Mitteilung
sonstigen Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the
communication of its contents to others without express authorization is prohibited.