

product data sheet

item no. 70.352.1035.2

hood BAS GOT GC 10 M20 A2

Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M20 on the top, low version, 10-poles

item no.	70.352.1035.2
EAN	4015573616912
order unit	1 piece(s)

certificates / approvals



technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	10
model of the housing	male
locking mechanism	double locking levers
cable entry	above
type of cable	intermediate support
with cable screw gland	no
thread size M	20
thread size PG	
hinged lid	no
EMC-version	no
length	73 mm
width	43 mm
height	53 mm

