

## product data sheet

item no. 70.350.1035.2

### hood BAS GOT GA 10 M20 A2

Hood revos basic made of aluminum, for double locking lever or.  
screw cap with nozzle M20 on the right side, low version, 10-poles

|            |               |
|------------|---------------|
| item no.   | 70.350.1035.2 |
| EAN        | 4015573598485 |
| order unit | 1 piece(s)    |

## certificates / approvals




## technical data

### general

|                                                          |                     |
|----------------------------------------------------------|---------------------|
| housing material                                         | aluminum            |
| color                                                    | grey                |
| surface                                                  | with powder coating |
| degree of protection (IP)                                | other               |
| UV resistant                                             | yes                 |
| flammability class of insulation material acc. with UL94 | other               |
| operating temperature range min.                         | -40 °C              |
| operating temperature range max.                         | 120 °C              |

### model

|                        |                       |
|------------------------|-----------------------|
| construction           | 10                    |
| model of the housing   | male                  |
| locking mechanism      | double locking levers |
| cable entry            | sideways              |
| type of cable          | intermediate support  |
| with cable screw gland | no                    |
| thread size M          | 20                    |
| thread size PG         |                       |
| hinged lid             | no                    |
| EMC-version            | no                    |
| length                 | 73 mm                 |
| width                  | 43 mm                 |
| height                 | 53 mm                 |



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung  
seiner Inhalte sind verboten, soweit nicht ausdrücklich gestattet.  
The reproduction, distribution and utilization of this document as well as the  
communication of its contents to others without express authorization is prohibited.

70.350.1035.0 13K\_2 09.03.2025 freeshaun 2013-03-08-20108-04-38 1.000