


product data sheet

item no. 76.330.1035.1

bottom BAS GUT GL 10HM25 50 A1

Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the right and left side, low version, 10-polig



item no.	76.330.1035.1
EAN	4015573808423
order unit	1 piece(s)

certificates / approvals

technical data

general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model



construction	10
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	two-sided
type of cable	thread
with cable screw gland	no
thread size M	25
thread size PG	
hinged lid	no
EMC-version	no
length	97 mm
width	58 mm
height	72 mm

Ausführung .1
version .1


Gewinde M25 (2x)
thread M25 (2x)



Verschraubung M25
screw connection M25



Gezeichnete Ausführung .0 / version .0



weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-nr.	Typ type
76.330.1035.0	BAS GUT GL 10HM25 50 A0
76.330.1035.1	BAS GUT GL 10HM25 50 A1

Freitoleranz nach -				CAD - Zeichnung, keine manuellen Änderungen				1.Verwendung: -			Bl.: 1 von 1	
	/	Maßstab	Werkstoff und Oberfläche:		2004	Tag	Name		T	Zeichnung Nr.		Index
	/	%			Entworfen	18.10.	Daetsch T.					
	/				Geprüft	-	-					
	/	Vol.	mm²	Bl.	mm²	Normgepr.		-	-	Ersatz für: -		
	/											
	/											
Buchseite		Datum / Blatt		 wieland		Benennung		GEHAEUSEUNTERTEIL HOUSING LOWER PART Größe 10 / size 10 2x M25				
Änderung												

Weitergabe sowie Vervielfältigung dieser Dokumente, Vervielfältigung und Mitteilung
sonstigen Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the
communication of its contents to others without express authorization is prohibited.