


## product data sheet

item no. 71.320.1028.0

### bottom BAS GUT GK 10 A

Bottom-base revos basic made of aluminum, with single locking lever, open, low version, 10-poles



|            |               |
|------------|---------------|
| item no.   | 71.320.1028.0 |
| EAN        | 4015573225152 |
| order unit | 1 piece(s)    |

### certificates / approvals



### technical data

#### general

|                                                            |                     |
|------------------------------------------------------------|---------------------|
| housing material                                           | aluminum            |
| color                                                      | grey                |
| surface                                                    | with powder coating |
| degree of protection (IP)                                  | IP54                |
| UV resistant                                               | yes                 |
| inflammability class of insulation material acc. with UL94 | other               |
| operating temperature range min.                           | -40 °C              |
| operating temperature range max.                           | 120 °C              |

#### model

|                        |                                  |
|------------------------|----------------------------------|
| construction           | 10                               |
| model of the housing   | equipment mounted (feed-through) |
| locking mechanism      | single locking lever             |
| cable entry            | none                             |
| type of cable          | none                             |
| with cable screw gland | no                               |
| thread size PG         |                                  |
| hinged lid             | no                               |
| EMC-version            | no                               |
| length                 | 93 mm                            |
| width                  | 43.5 mm                          |
| height                 | 28 mm                            |

