

## product data sheet

item no. 76.353.1035.1

### hood BAS GOT GG 10HM32 50 A1

Hood revos basic made of aluminum, for single locking lever with threaded hole M32 on the right side, low version, 10-poles



|            |               |
|------------|---------------|
| item no.   | 76.353.1035.1 |
| EAN        | 4015573844377 |
| order unit | 1 piece(s)    |

## certificates / approvals

## technical data

### general

|                                                          |                     |
|----------------------------------------------------------|---------------------|
| housing material                                         | aluminum            |
| color                                                    | grey                |
| surface                                                  | with powder coating |
| degree of protection (IP)                                | other               |
| UV resistant                                             | yes                 |
| flammability class of insulation material acc. with UL94 | other               |
| operating temperature range min.                         | -40 °C              |
| operating temperature range max.                         | 120 °C              |

### model

|                        |                      |
|------------------------|----------------------|
| construction           | 10                   |
| model of the housing   | male                 |
| locking mechanism      | single locking lever |
| cable entry            | sideways             |
| type of cable          | thread               |
| with cable screw gland | no                   |
| thread size M          | 32                   |
| thread size PG         |                      |
| hinged lid             | no                   |
| EMC-version            | no                   |
| length                 | 89 mm                |
| width                  | 43 mm                |
| height                 | 70 mm                |

