

## product data sheet

item no. 71.372.1035.0

### hood BAS GOT GL 10 M20 A0

Hood revos basic made of aluminum, with single locking lever and cable gland M20 on the top - free cable connection (IP54), low version, 10-poles



|            |               |
|------------|---------------|
| item no.   | 71.372.1035.0 |
| EAN        | 4015573627406 |
| order unit | 1 piece(s)    |

## certificates / approvals



## technical data

### general

|                                                            |                     |
|------------------------------------------------------------|---------------------|
| housing material                                           | aluminum            |
| color                                                      | grey                |
| surface                                                    | with powder coating |
| degree of protection (IP)                                  | IP54                |
| UV resistant                                               | yes                 |
| inflammability class of insulation material acc. with UL94 | other               |
| operating temperature range min.                           | -40 °C              |
| operating temperature range max.                           | 120 °C              |

### model

|                        |                      |
|------------------------|----------------------|
| construction           | 10                   |
| model of the housing   | cable coupler        |
| locking mechanism      | single locking lever |
| cable entry            | above                |
| type of cable          | gland nut            |
| with cable screw gland | yes                  |
| thread size M          | 20                   |
| thread size PG         |                      |
| hinged lid             | no                   |
| EMC-version            | no                   |
| length                 | 89 mm                |
| width                  | 43 mm                |
| height                 | 53 mm                |

