


product data sheet

item no. 70.330.0635.1

bottom BAS GUT GL 6 M20 A1

Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M20 on the right and left side, low version, 6-polig



item no.	70.330.0635.1
EAN	4015573599505
order unit	1 piece(s)

certificates / approvals



technical data


general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP65
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	6
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	two-sided
type of cable	thread
with cable screw gland	no
thread size M	20
thread size PG	
hinged lid	no
EMC-version	no
length	84 mm
width	52 mm
height	54.7 mm

F



Technical drawing of a rectangular plate. The dimensions are 70 (width) and 40 (height). The hole diameter is $\varnothing 5,3 / M5$.

Tolerierung Size ISO 14005  Tolerance system Size ISO 14005  (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).					ja/yes ☒ Stoffverfalls- und Deklarationsliste nach (U-TP-05/03 ist einzuhalten. Conformity with Wieland document U-TP-05/03 (list of prohibited / delectable hazardous substances) to be declared!						
Freitoleranz nach General tolerance			CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed			1.Verwendung: First Use: -		Blatt: Sheet: 1 von 1			
		/ 	Werkstoff/Material		2013 Tag/Date		Name		Zeichnung Nr./Drawing No.		Index
		/ 	Aluminium		hergestellt drawn		02.05.		Treschen		T
		/ 	beschichtet/coated		geprüft checked		-		-		70.330.0635.0 13K
		/ 	Maßstab/Scale		Nurprüf: Stand. check		-		-		Maße in mm/Dimensions are in mm
		/ 1:2	grau/grey								
		/ Vol.	mm		Öff./Surf.		mm		Ersatz für/Replacement for: -		
		/ 	wieland		Type		Benennung/Title				
		/ 			revos		GEHAUSEUNTERTEIL				
		/ 			BASIC		Baugröße 6-Kabelabgang 2x M20/M25				
		/ 					Housing size 6-cable outlet 2x M20/M25				
Index		Datum / Blatt Date / Sheet		Elektrische Verbindungen							
Änderung/Revision											

703300635013K_2 CADW3028 Treschan 2013-09-20T11:20:49 1.000