

product data sheet

item no. 55.703.1053.0

feed-through terminal WKF2,5/MD/15

Feed-through terminal with tension spring connection for mounting on TS15, nominal cross section: 2.5 mm², width: 10 mm, color: grey



item no.	55.703.1053.0
EAN	4015573375529
order unit	100 piece(s)

certificates / approvals



technical data

general

nominal cross section	2.5 mm ²
color	grey
number of levels	1
number of clamp positions per level	4
width/grid dimension	10 mm
insulating housing	PA66
flammability class of insulation material acc. with UL94	V2
explosion-tested version "Ex e"	no
mounting method	DIN rail (top hat rail) 15 mm
terminal blocks for electrical installations	yes
Anzahl der Klemmstellen je Etage	4
Montageart	DIN rail (top hat rail) 15 mm
Brennbarkeitsklasse des Isolierstoffs	V2
Reihenklemmen für Installationsverteiler	yes

technical data

rated current	24 A
rated voltage	800 V
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	36 mm

connection data

connection type 1	spring clamp connection
connection type 2	spring clamp connection

minimum cross section solid	0.13 mm ²
maximum cross section solid	4 mm ²
minimum cross section fine stranded	0.13 mm ²
maximum cross section fine stranded	2.5 mm ²
wire strip length	11 mm

technical data UL/CSA

cross section UL	22-12 AWG
voltage UL	600 V
current factory wiring	20 A
current field wiring	20 A
cross section CSA	24-12 AWG
voltage CSA	600 V
current CSA	20 A

accessories

item no.	type	description
98.090.0015.0	mounting rail TS 15 PERF - l:2000mm	Mounting rail TS 15, slotted, Höhe 5,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
07.312.2953.0	end plate APF 2,5 / M..	End plate for DIN rail terminal blocks type WKF 2,5/M..., color: grey
07.312.2953.6	end plate APF 2,5 / M.. BLAU	End plate for DIN rail terminal blocks type WKF 2,5/M..., color: blue
07.312.2953.9	end plate APF 2,5 / M.. ORANGE	End plate for DIN rail terminal blocks type WKF 2,5/M..., color: orange

