


product data sheet

item no. 56.703.9753.0

installation terminal WKIF 2,5 D-D

Installation rail terminal blocks with tension spring connection for mounting on TS 35, nominal cross section: 2.5 mm², width: 5 mm, color: grey



item no.	56.703.9753.0
EAN	4015573564442
order unit	50 piece(s)

certificates / approvals



technical data

general

nominal cross section	2.5 mm ²
basic color	grey
number of levels	2
number of clamp positions per level	2
width/grid dimension	5 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail) 35/7.5 mm
terminal blocks for electrical installations	yes

technical data

rated current	24 A
rated voltage	400 V
rated impulse voltage	4 kV
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	95 mm


connection data

connection type 1	spring clamp connection
connection type 2	spring clamp connection
minimum cross section solid	0.14 mm ²
maximum cross section solid	4 mm ²
minimum cross section fine stranded	0.14 mm ²
maximum cross section fine stranded	2.5 mm ²

wire strip length	11 mm
-------------------	-------


technical data UL/CSA

cross section UL	22-12 AWG
current factory wiring	20 A
current field wiring	20 A
cross section CSA	22-14 AWG
voltage CSA	300 V
current CSA	20 A



Hutschiene EN 60715-35x7,5
mounting rail EN 60715-35x7,5

Hutschiene EN 60715-35x15
mounting rail EN 60715-35x15



Weitere Daten siehe Katalog
further data see catalog

Freitoleranz nach -				CAD - Zeichnung, keine manuellen Änderungen				1. Verwendung: -				Bl.: 1 von 1		
	/	Maßstab		Werkstoff und Oberfläche:		2003		Tag		Name		Zeichnung Nr. 56.703.9753.0 01K		Index
	/	2:1				Entworfen		13.05.		Schmitt J.				
	/					Geprüft		-		-				
	/	Vol.		mm ² Dr.		mm ²		Normgepr.		-		Ersatz für: -		
	/													
	/													
						wieland		WKIF 2,5		Benennung		INSTALLATIONSKLEMME installation terminal		
								D-D						
Buchstabe		Datum / Blatt												
Änderung														

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

A	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	M1	M2	M3	L	G	1	1.1	2.1	1.1
---	---	---	---	---	---	---	---	---	---	----	----	----	----	----	----	----	----	----	----	----	----	----	----	---	---	---	-----	-----	-----