


## product data sheet

item no. 56.704.4055.0

### fuse terminal WKFN 4 TKG/35

Disconnect block with tension spring connection for mounting on TS 35, nominal cross section: 4 mm<sup>2</sup>, width: 6 mm, color: grey



|            |               |
|------------|---------------|
| item no.   | 56.704.4055.0 |
| EAN        | 4015573935730 |
| order unit | 100 piece(s)  |

### certificates / approvals



### technical data

#### general

|                                                          |                                   |
|----------------------------------------------------------|-----------------------------------|
| nominal cross section                                    | 4 mm <sup>2</sup>                 |
| color                                                    | grey                              |
| number of levels                                         | 1                                 |
| number of clamp positions per level                      | 2                                 |
| width/grid dimension                                     | 6 mm                              |
| insulating housing                                       | PA666                             |
| flammability class of insulation material acc. with UL94 | V0                                |
| mounting method                                          | DIN rail (top hat rail) 35/7.5 mm |
| terminal blocks for electrical installations             | no                                |
| Anzahl der Klemmstellen je Etage                         | 2                                 |
| Montageart                                               | DIN rail (top hat rail) 35/7.5 mm |
| Brennbarkeitsklasse des Isolierstoffs                    | V0                                |
| Reihenklemmen für Installationsverteiler                 | no                                |

#### technical data

|                             |               |
|-----------------------------|---------------|
| rated voltage               | 500 V         |
| rated impulse voltage       | 8 kV          |
| pollution degree            | 3             |
| closing plate required      | yes           |
| type of insulation material | thermoplastic |
| length                      | 82.2 mm       |

#### connection data

|                             |                         |
|-----------------------------|-------------------------|
| connection type 1           | spring clamp connection |
| connection type 2           | spring clamp connection |
| minimum cross section solid | 0.13 mm <sup>2</sup>    |

|                                     |                      |
|-------------------------------------|----------------------|
| maximum cross section solid         | 6 mm <sup>2</sup>    |
| minimum cross section fine stranded | 0.13 mm <sup>2</sup> |
| maximum cross section fine stranded | 4 mm <sup>2</sup>    |
| wire strip length                   | 11 mm                |

#### accessories

| item no.      | type                                             | description                                                                                                                                          |
|---------------|--------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Z7.261.1227.0 | jumper bar IVB WKF 4 - 2                         | Cross connector, insulated for DIN rail terminal blocks type WKF..., 2 -pole                                                                         |
| Z7.261.1327.0 | jumper bar IVB WKF 4 - 3                         | Cross connector, insulated for DIN rail terminal blocks type WKF..., 3 -pole                                                                         |
| Z7.261.1427.0 | jumper bar IVB WKF 4 - 4                         | Cross connector, insulated for DIN rail terminal blocks type WKF..., 4 -pole                                                                         |
| Z7.261.1527.0 | jumper bar IVB WKF 4 - 5                         | Cross connector, insulated for DIN rail terminal blocks type WKF..., 5 -pole                                                                         |
| Z7.261.1627.0 | jumper bar IVB WKF 4 - 6                         | Cross connector, insulated for DIN rail terminal blocks type WKF..., 6 -pole                                                                         |
| Z7.261.1727.0 | jumper bar IVB WKF 4 - 7                         | Cross connector, insulated for DIN rail terminal blocks type WKF..., 7 -pole                                                                         |
| Z7.261.1827.0 | jumper bar IVB WKF 4 - 8                         | Cross connector, insulated for DIN rail terminal blocks type WKF..., 8 -pole                                                                         |
| Z7.261.1927.0 | jumper bar IVB WKF 4 - 9                         | Cross connector, insulated for DIN rail terminal blocks type WKF..., 9 -pole                                                                         |
| Z7.261.2027.0 | jumper bar IVB WKF 4 - 10                        | Cross connector, insulated for DIN rail terminal blocks type WKF..., 10 -pole                                                                        |
| 98.300.0000.0 | mounting rail TS 35x7,5 UNPERF - l:2000mm        | Mounting rail TS 35, unslotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated                                            |
| 98.300.1000.0 | mounting rail TS 35x7,5 PERF 15mm - l:2000mm     | Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated                                              |
| 98.300.1800.0 | mounting rail TS 35x7,5 PERF 18mm - l:2000mm     | Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated                                              |
| 98.300.1900.0 | mounting rail TS 35x7,5 PERF 25mm - l:2000mm     | Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated                                              |
| 98.360.0000.0 | mounting rail TS 35x15-2,3 UNPERF - l:2000mm     | Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated                                             |
| 98.360.0004.0 | mounting rail TS 35x15-2,3 UNPERF FZN - l:2000mm | Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel, hot galvanized                                                               |
| 98.370.0000.0 | mounting rail TS 35x15 UNPERF - l:2000mm         | Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and dichromated                                            |
| 98.370.1000.0 | mounting rail TS 35x15 PERF 15mm - l:2000mm      | Mounting rail TS 35, slotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated                                               |
| 98.380.0000.0 | mounting rail TS 35x15-2,3 UNPERF CU - l:2000mm  | Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material E copper                                                                            |
| 07.312.9055.0 | end plate APFN 4 D2/2                            | End plate for DIN rail terminal blocks type WKFN 4 D2/2..., color: grey                                                                              |
| 07.313.1655.0 | intermediate plate ZP/WKFN 4 TKG                 | Intermediate for DIN rail terminal blocks type WKFN 4 TKG..., color: grey                                                                            |
| 04.242.6053.0 | marking tag strips 9705 A / 6 / 10               | Marking tag strips for DIN rail terminal blocks type 9700 A / 6..., 10 tags per strip, color: white, unmarked, markable with Wieplot plotter- system |

