


product data sheet

item no. 56.702.7653.0

multi-tier terminal WKF 1,5 E2/35

Duo Feed-through terminal with tension spring connection for mounting on TS 35, nominal cross section: 1.5 mm², width: 4.15 mm, color: grey



item no.	56.702.7653.0
EAN	4015573731868
order unit	50 piece(s)

certificates / approvals



technical data

general

nominal cross section	1.5 mm ²
color	grey
number of levels	2
number of clamp positions per level	2
width/grid dimension	4.15 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V0
explosion-tested version "Ex e"	yes
mounting method	DIN rail (top hat rail) 35/7.5 mm
terminal blocks for electrical installations	yes
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail) 35/7.5 mm
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	yes

technical data

rated current	17.5 A
rated voltage	500 V
rated impulse voltage	6 kV
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	67.6 mm

connection data

connection type 1	spring clamp connection
-------------------	-------------------------

connection type 2	spring clamp connection
minimum cross section solid	0.08 mm ²
maximum cross section solid	1.5 mm ²
minimum cross section fine stranded	0.08 mm ²
maximum cross section fine stranded	1.5 mm ²
wire strip length	10 mm



technical data UL/CSA

cross section UL	26-14 AWG
voltage UL	300 V
current factory wiring	15 A
current field wiring	15 A
cross section CSA	26-14 AWG
voltage CSA	300 V
current CSA	15 A

accessories

item no.	type	description
Z7.268.0227.0	jumper bar IVB WKF 1,5- 2	Cross connector, insulated for DIN rail terminal blocks type WKF..., 2 -pole
Z7.268.0327.0	jumper bar IVB WKF 1,5- 3	Cross connector, insulated for DIN rail terminal blocks type WKF..., 3 -pole
Z7.268.0427.0	jumper bar IVB WKF 1,5- 4	Cross connector, insulated for DIN rail terminal blocks type WKF..., 4 -pole
Z7.268.0527.0	jumper bar IVB WKF 1,5- 5	Cross connector, insulated for DIN rail terminal blocks type WKF..., 5 -pole
Z7.268.1027.0	jumper bar IVB WKF 1,5- 10	Cross connector, insulated for DIN rail terminal blocks type WKF..., 10-pole
Z7.268.2027.0	jumper bar IVB WKF 1,5- 20	Cross connector, insulated for DIN rail terminal blocks type WKF..., 20-pole
98.300.0000.0	mounting rail TS 35x7,5 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1000.0	mounting rail TS 35x7,5 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1800.0	mounting rail TS 35x7,5 PERF 18mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1900.0	mounting rail TS 35x7,5 PERF 25mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0000.0	mounting rail TS 35x15-2,3 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0004.0	mounting rail TS 35x15-2,3 UNPERF FZN - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel, hot galvanized
98.370.0000.0	mounting rail TS 35x15 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and dichromated
98.370.1000.0	mounting rail TS 35x15 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.380.0000.0	mounting rail TS 35x15-2,3 UNPERF CU - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material E copper
04.343.6953.8	warning cover ADF 1,5/5	Cover with warning symbol for DIN rail terminal blocks type WKF ...
07.312.8753.0	end plate APF 1,5 E2	End plate for DIN rail terminal blocks type WKF 1,5 E2..., color: grey
07.312.8853.0	partition TWF 1,5 E2	Partition for DIN rail terminal blocks type WKF 1,5 E2..., color: grey
Z4.243.2053.0	marking tag plate BZ/WKF 1,5/10	plate with marking tags for DIN rail terminal blocks type WKF 1,5, unmarked, markable with Wieprint printing-system

○ Diese Maße werden bei Abnahme besonders geprüft
Ausichtlich Prüfprobe
Mit JE bezeichneten Maßen sind nur JE-Interne Zwischenmaße



Hutschiene EN 60715-35x7,5
mounting rail EN 60715-35x7,5

Hutschiene EN 60715-35x15
mounting rail EN 60715-35x15

Weitere Daten siehe Katalog
further data see catalog

Teile-Nr./part-nr.	Typ/type	Farbe/colour
56.702.7653.0	WKF 1,5/E2/35	kieselgrau/grey

Freitoleranz nach DIN			CAD - Zeichnung, keine manuellen Änderungen			1. Verwendung: -		Bl.: 1 von 1		
	/	Maßstab	Werkstoff und Oberfläche:		2004	Tag	Name	T	Zeichnung Nr. 56.702.7653.0 01K	Index
	/	2:1			Entworfen	26.01.	Schmitt J.			
	/				Geprüft	-	-			
	/				Normgepr.	-	-			
	/	 wieland Elektrische Verbindungen	Ersatz für: -							
	/									
	/									
Buchstabe	Datum / Blatt				Benennung ETAGENKLEMME Federkraftanschluß Double-deck-terminal with spring clamp					
Änderung										

Weitergabe sowie Vervielfältigung dieser Dokumente, Vervielfältigung und Mitteilung
sonstigen Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the
communication of its contents to others without express authorization is prohibited.