


product data sheet

item no. 57.503.7255.0

initiator terminal WK 2,5-4 KOI /U-PGN /V0

Initiator terminal with Screw connection for mounting on TS 35 / TS 32, nominal cross section: 2.5 mm², width: 5 mm, color: grey



item no.	57.503.7255.0
EAN	4015573604438
order unit	50 piece(s)

certificates / approvals



technical data

general

nominal cross section	2.5 mm ²
color	grey
number of levels	1
number of clamp positions per level	4
width/grid dimension	5 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail)/G-rail
terminal blocks for electrical installations	yes
Anzahl der Klemmstellen je Etage	4
Montageart	DIN rail (top hat rail)/G-rail
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	yes

technical data

rated current	16 A
rated voltage	24 V
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	92 mm

connection data

connection type 1	screw connection
connection type 2	screw connection
minimum cross section solid	0.5 mm ²

maximum cross section solid	4 mm ²
minimum cross section fine stranded	0.5 mm ²
maximum cross section fine stranded	2.5 mm ²
wire strip length	10 mm
torque conductor mounting	0.4 Nm

technical data UL/CSA

cross section UL	22-12 AWG
voltage UL	24 V
current factory wiring	30 A
current field wiring	20 A
cross section CSA	22-12 AWG
voltage CSA	24 V
current CSA	25 A

accessories

item no.	type	description
07.257.0227.0	cross connector VB WK2,5 KO - 2	Jumper comp for DIN rail terminal blocks type WK ..., 2 -pole
07.257.0327.0	cross connector VB WK2,5 KO - 3	Jumper comp for DIN rail terminal blocks type WK ..., 3 -pole
07.257.0427.0	cross connector VB WK2,5 KO - 4	Jumper comp for DIN rail terminal blocks type WK ..., 4 -pole
07.257.0527.0	cross connector VB WK2,5 KO - 5	Jumper comp for DIN rail terminal blocks type WK ..., 5 -pole
07.257.0627.0	cross connector VB WK2,5 KO - 6	Jumper comp for DIN rail terminal blocks type WK ..., 6 -pole
07.257.0727.0	cross connector VB WK2,5 KO - 7	Jumper comp for DIN rail terminal blocks type WK ..., 7 -pole
07.257.0827.0	cross connector VB WK2,5 KO - 8	Jumper comp for DIN rail terminal blocks type WK ..., 8 -pole
07.257.0927.0	cross connector VB WK2,5 KO - 9	Jumper comp for DIN rail terminal blocks type WK ..., 9 -pole
07.257.1027.0	cross connector VB WK2,5 KO - 10	Jumper comp for DIN rail terminal blocks type WK ..., 10 -pole
07.257.1127.0	cross connector VB WK2,5 KO - 11	Jumper comp for DIN rail terminal blocks type WK ..., 11 -pole
07.257.1227.0	cross connector VB WK2,5 KO - 12	Jumper comp for DIN rail terminal blocks type WK ..., 12 -pole
07.257.2027.0	cross connector VB WK2,5 KO - 20	Jumper comp for DIN rail terminal blocks type WK ..., 20 -pole
98.190.0000.0	mounting rail TS 32 UNPERF - l:2000mm	Mounting rail G 32, unslotted, Höhe 5,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.190.1000.0	mounting rail TS 32 PERF 15mm - l:2000mm	Mounting rail G 32, slotted, Höhe 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.210.0000.0	mounting rail TS 32 UNPERF AL - l:2000mm	Mounting rail G 32, unslotted, Höhe 15 mm, length 2 m, material Aluminium
98.220.0000.0	mounting rail TS 32 UNPERF CU - l:2000mm	Mounting rail G 32, unslotted, Höhe 15 mm, length 2 m, material E copper
98.300.0000.0	mounting rail TS 35x7,5 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1000.0	mounting rail TS 35x7,5 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1800.0	mounting rail TS 35x7,5 PERF 18mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.300.1900.0	mounting rail TS 35x7,5 PERF 25mm - l:2000mm	Mounting rail TS 35, slotted, size 7,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0000.0	mounting rail TS 35x15-2,3 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.360.0004.0	mounting rail TS 35x15-2,3 UNPERF FZN - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel, hot galvanized
98.370.0000.0	mounting rail TS 35x15 UNPERF - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and dichromated
98.370.1000.0	mounting rail TS 35x15 PERF 15mm - l:2000mm	Mounting rail TS 35, slotted, size 15 mm, length 2 m, material steel. galv. zinc-plated and passivated
98.380.0000.0	mounting rail TS 35x15-2,3 UNPERF CU - l:2000mm	Mounting rail TS 35, unslotted, size 15 mm, length 2 m, material E copper
07.310.9355.0	end plate AP 2,5-4 KO/V0	End plate for DIN rail terminal blocks type WK 2,5-4 KO..., color: grey
07.310.9455.0	partition TW 2,5-4 KO/V0	Partition for DIN rail terminal blocks type WK 2,5-4 KO..., color: grey

