

product data sheet

item no. 57.904.5155.0

compensating terminal 9785U/50 KOHM-SPT/V0

Compensating terminal block with screw connection for mounting on TS 35 and TS 32, nominal cross section 4 mm², width 12 mm, color grey

item no.	57.904.5155.0
EAN	4015573605732
order unit	50 piece(s)

certificates / approvals

technical data

general

nominal cross section	2.5 mm ²
color	grey
number of levels	2
number of clamp positions per level	2
width/grid dimension	12 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail)/G-rail
terminal blocks for electrical installations	no
type of component	potenziometer
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail)/G-rail
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklappen für Installationsverteiler	no

technical data

pollution degree	3
closing plate required	no
type of insulation material	thermoplastic
length	49 mm

connection data

connection type 1	screw connection
connection type 2	screw connection
minimum cross section solid	0.5 mm ²
maximum cross section solid	2.5 mm ²
minimum cross section fine stranded	0.5 mm ²
maximum cross section fine stranded	2.5 mm ²
wire strip length	9 mm
torque conductor mounting	0.5 Nm

accessories

item no.	type	description
07.253.0227.0	cross connector VB 9786 2	Jumper comp for DIN rail terminal blocks type 9786 ..., 2 -pole
07.253.0327.0	cross connector VB 9786 3	Jumper comp for DIN rail terminal blocks type 9786 ..., 3 -pole
07.253.0427.0	cross connector VB 9786 4	Jumper comp for DIN rail terminal blocks type 9786 ..., 4 -pole
07.253.0527.0	cross connector VB 9786 5	Jumper comp for DIN rail terminal blocks type 9786 ..., 5 -pole
07.253.0627.0	cross connector VB 9786 6	Jumper comp for DIN rail terminal blocks type 9786 ..., 6 -pole