


product data sheet

item no. 57.106.1155.0

stud terminal WRT 6

Ring lug terminal block with ring lug connection M4 for mounting on TS35, nominal cross section: 6 mm², width: 11 mm, color: grey



item no.	57.106.1155.0
EAN	4049088144004
order unit	50 piece(s)

certificates / approvals



technical data

general

nominal cross section	6 mm ²
color	grey
number of levels	1
number of clamp positions per level	2
width/grid dimension	11 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V2
mounting method	DIN rail (top hat rail) 35 mm
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail) 35 mm
Brennbarkeitsklasse des Isolierstoffs	V2

technical data

rated current	41 A
rated voltage	1000 V
rated impulse voltage	8 kV
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	46 mm

connection data

connection type 1	bolt connection
connection type 2	bolt connection
minimum cross section fine stranded	1.5 mm ²
maximum cross section fine stranded	6 mm ²

minimum cross section stranded	1.5 mm ²
maximum cross section stranded	6 mm ²
torque conductor mounting	1.2 Nm

technical data UL/CSA

cross section UL	22-8 AWG
voltage UL	600 V
current factory wiring	50 A

