

product data sheet

item no. 56.398.1055.0

feed-through terminal RFK 1 / 185 FM S35/V0

Feed-through terminal with Screw connection for mounting on TS 35/7,5 mm, nominal cross section: 185 mm², width: 42 mm, color: grey



item no.	56.398.1055.0
EAN	4015573568778
order unit	10 piece(s)

certificates / approvals



technical data

general

nominal cross section	185 mm ²
color	grey
number of levels	1
number of clamp positions per level	2
width/grid dimension	42 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V0
explosion-tested version "Ex e"	no
mounting method	DIN rail (top hat rail) 35/7.5 mm
terminal blocks for electrical installations	no
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail) 35/7.5 mm
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	no

technical data

rated current	353 A
rated voltage	1000 V
rated impulse voltage	8 kV
pollution degree	3
closing plate required	no
type of insulation material	thermoplastic
length	92 mm

connection data

connection type 1	screw connection
-------------------	------------------

connection type 2	screw connection
maximum cross section fine stranded	185 mm ²
maximum cross section stranded	185 mm ²
torque conductor mounting	14 Nm

technical data UL/CSA

cross section UL	0 AWG-400 kcmil
voltage UL	600 V
current factory wiring	375 A
current field wiring	375 A
cross section CSA	0 AWG-400 kcmil
voltage CSA	600 V
current CSA	375 A

