

Product data sheet

Item No. 99.702.3329.7

Bottom EX GUT GX16 09IA Z

Item No.	99.702.3329.7
EAN	4015573301825
Order Unit	10 Piece(s)

Certificates / Approvals



Technical data

General

Housing material	Die-cast zinc
Color	Blue
Surface	With powder coating
Degree of protection (IP)	IP54
Operating temperature range min.	-20 °C
Operating temperature range max.	60 °C

Model

Construction	16
Model of the housing	female
Locking mechanism	Double locking levers
Cable entry	None
Type of cable	None
With cable screw gland	No
Thread size PG	
EMC-version	No
Length	113 mm
Width	66 mm
Height	46 mm