


product data sheet

item no. 71.441.2437.1

bottom BAS GUM GS 24 M25 B1

Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the left side, with protective cover, low version, 24-polig



item no.	71.441.2437.1
EAN	4049088365133
order unit	1 piece(s)

certificates / approvals




technical data

general

housing material	aluminum
color	grey
surface	bare
degree of protection (IP)	IP66
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	24
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	sideways
type of cable	thread
with cable screw gland	no
thread size M	25
thread size PG	
hinged lid	yes
EMC-version	no
length	144 mm
width	57 mm
height	57 mm



Wiedergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung
seiner Inhalte sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the
communication of its contents to others without express authorization is prohibited.