

product data sheet

item no. 71.450.2437.1

hood BAS GOM GG24 M25 B1

Hood revos basic metal-series without coating, for single locking lever with threaded hole M25 on the right side, low version, 24-poles



item no.	71.450.2437.1
EAN	4049088350719
order unit	1 piece(s)

certificates / approvals




technical data

general

housing material	aluminum
color	grey
surface	bare
degree of protection (IP)	IP66
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	24
locking mechanism	single locking lever
cable entry	sideways
type of cable	thread
with cable screw gland	no
thread size M	25
thread size PG	
hinged lid	no
EMC-version	no
length	138 mm
width	43 mm
height	70 mm



Wieland-Electric ist eine Marke der Wieland-Werkzeugmaschinen GmbH. Die Reproduktion, Verbreitung und Nutzung dieser Zeichnung ist ohne schriftliche Genehmigung der Wieland-Werkzeugmaschinen GmbH. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.