

## product data sheet

item no. 71.353.2435.3

hood BAS GOT GG 24 M32 A3

Hood revos basic made of aluminum, for single locking lever with trumpet gland M32 on the right side (IP54), low version, 24-poles

|            |               |
|------------|---------------|
| item no.   | 71.353.2435.3 |
| EAN        | 4015573651715 |
| order unit | 1 piece(s)    |

## certificates / approvals



## technical data

### general

|                                                          |                     |
|----------------------------------------------------------|---------------------|
| housing material                                         | aluminum            |
| color                                                    | grey                |
| surface                                                  | with powder coating |
| degree of protection (IP)                                | IP54                |
| UV resistant                                             | yes                 |
| flammability class of insulation material acc. with UL94 | other               |
| operating temperature range min.                         | -40 °C              |
| operating temperature range max.                         | 120 °C              |

### model

|                        |                      |
|------------------------|----------------------|
| construction           | 24                   |
| model of the housing   | male                 |
| locking mechanism      | single locking lever |
| cable entry            | sideways             |
| type of cable          | gland nut            |
| with cable screw gland | yes                  |
| thread size M          | 32                   |
| thread size PG         |                      |
| hinged lid             | no                   |
| EMC-version            | no                   |
| length                 | 136 mm               |
| width                  | 43 mm                |
| height                 | 70 mm                |

