

product data sheet

item no. 70.425.0637.0

bottom BAS GUM GP 6 B

Bottom-base revos basic metal-series without coating, with single locking lever and protective cover, low version, 6-poles



item no.	70.425.0637.0
EAN	4049088343230
order unit	1 piece(s)

certificates / approvals


technical data

general

housing material	aluminum
color	grey
surface	bare
degree of protection (IP)	IP66
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	6
model of the housing	equipment mounted (feed-through)
locking mechanism	single locking lever
cable entry	none
type of cable	none
with cable screw gland	no
thread size PG	
hinged lid	yes
EMC-version	no
length	80 mm
width	43.5 mm
height	50 mm



Wiedergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung
seiner Inhalte sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the
communication of its contents to others without express authorization is prohibited.