

## product data sheet

item no. 70.420.0637.0

### bottom BAS GUM GK 6 B

Bottom-base revos basic metal-series without coating, open, low version, 6-poles



|            |               |
|------------|---------------|
| item no.   | 70.420.0637.0 |
| EAN        | 4049088343223 |
| order unit | 1 piece(s)    |

## certificates / approvals

## technical data

### general

|                                                          |          |
|----------------------------------------------------------|----------|
| housing material                                         | aluminum |
| color                                                    | grey     |
| surface                                                  | bare     |
| degree of protection (IP)                                | IP66     |
| UV resistant                                             | yes      |
| flammability class of insulation material acc. with UL94 | other    |
| operating temperature range min.                         | -40 °C   |
| operating temperature range max.                         | 120 °C   |

### model

|                        |                                  |
|------------------------|----------------------------------|
| construction           | 6                                |
| model of the housing   | equipment mounted (feed-through) |
| locking mechanism      | single locking lever             |
| cable entry            | none                             |
| type of cable          | none                             |
| with cable screw gland | no                               |
| thread size PG         |                                  |
| hinged lid             | no                               |
| EMC-version            | no                               |
| length                 | 80 mm                            |
| width                  | 43.5 mm                          |
| height                 | 30 mm                            |

