


product data sheet

item no. 70.337.0635.1

bottom BAS GUT GO 6 M25 A1

Bottom-base revos basic made of aluminum, with single locking lever and threaded hole M25 on the bottom, low version, 6-poles



item no.	70.337.0635.1
EAN	4015573707955
order unit	1 piece(s)

certificates / approvals



technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP65
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	6
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	below
type of cable	thread
with cable screw gland	no
thread size M	25
thread size PG	
hinged lid	no
EMC-version	no
length	84 mm
width	52 mm
height	54.7 mm

