

product data sheet

item no. 73.351.0635.0

hood BAS GOT GH 6HM20 A0

Hood revos basic made of aluminum, for single locking lever with cable gland M20 on the front (IP54), high version, 6-poles



item no.	73.351.0635.0
EAN	4049088220074
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
flammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	6H
model of the housing	male
locking mechanism	single locking lever
cable entry	front side
type of cable	gland nut
with cable screw gland	yes
thread size M	20
thread size PG	
hinged lid	no
EMC-version	no
length	74 mm
width	43 mm
height	70 mm

