

product data sheet

item no. 05.544.7800.0

male contact CRIMP RST20i2/i3 1,0QMM

RST20i3/2 crimp contact, male, 20A, for cross section 1.0 mm²/AWG17



item no.	05.544.7800.0
EAN	4049088155895
order unit	100 piece(s)




certificates / approvals

technical data

technical data

nominal cross section	1 mm ²
type of construction	crimp contacts for 2-/3-pole
version of construction	male


Schnitt A-A:
section A-A:



Kennzeichnungsritze
(marking chamfer)

Verpackungseinheit 100 Stück pro Karton
packaging unit: 100 piece per carton

M 1:1
Scale



05.545.4600.0	4,0qmm	ohne/without	2,85 mm	3,9 mm
05.544.8000.0	2,5qmm	1 Rille/chamfer	2,35 mm	3,6 mm
05.544.7900.0	1,5qmm	ohne/without	1,90 mm	3,0 mm
05.544.7800.0	0,75 - 1,0qmm	1 Rille/chamfer	1,75 mm	2,6 mm
Teile-Nr. part-no.	Anschluss- querschnitt connection cross-section	Kenn- zeichnung marking	Ød _i	ØD _a

Freitoleranz nach			CAD - Zeichnung, keine manuellen Änderungen			1. Verwendung: 96.132.2053.1		Bl.: 1 von 1		
	/	Maßstab	Werkstoff und Oberfläche:		2011	Tag	Name	Zeichnung Nr.		Index
	/	5:1	a CuZn		Entworfen	28.11.	Ritter	T	05.544.7821.0 01K	
	/		Ag		Geprüft	-	-			
	/	Vol.	mm²	Ø i.	mm²	Normgepr.	-	Ersatz für: -		
b	30.01.2012/		 wieland			Benennung STECKERKONTAKT RST2012/3 male contact mit Crimpkontakt/with crimpcontact 0,75 - 4,0 gmm 				
a	13.12.2011/									
Buchstabe		Datum / Blatt		Elektrische Verbindungen						
Änderung										