

product data sheet

item no. 96.131.0053.0

connector RST20I3C B1 ZR1 GL

RST® CLASSIC connector, straight, number of poles 3, female, connection type crimp, rated voltage 250 V, rated current 20 A, cable diameter 6 - 10 mm, color of coding/ contact carrier light grey



item no.	96.131.0053.0
EAN	4049088140204
order unit	100 piece(s)

certificates / approvals



technical data

note

note	crimp contacts have to ordered separately (under fits with)
------	---

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	light grey
Pole codification	L, N, PE
color of housing inclusive strain relief	light grey
RAL-Nummer Codierung/Kontakteinsatz	7035

connection data

cable diameter max.	10 mm
cable diameter min.	6 mm
connection cross section fine stranded mm² max.	4 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
sheath strip length	37 mm
wire strip length	8 mm

model

model	female
connection type	crimp
degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
------------------	-----------

halogen free	yes
contact material	CuZn
fire load	0.289 kWh/St
insulation components continuous temperature	100 °C
surface finish	silver-plated

dimensions

length	82 mm
width	34.6 mm
height	34.6 mm

accessories

item no.	type	description
99.413.6205.2	cover for female connector GL	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color light grey
Z5.564.4553.0	cover for female connector GL	RST20i3/2 cover piece, for covering unused female connectors, color light grey
02.122.9000.0	female contact CRIMP RST20i2/i3 1,0QMM	RST20i3/2 crimp contact, female, 20A, for cross section 1.0 mm²/AWG17
02.122.9100.0	female contact CRIMP RST20i2/i3 1,5QMM	RST20i3/2 crimp contact, female, 20A, for cross section 1.5 mm²/AWG16
02.122.9200.0	female contact CRIMP RST20i2/i3 2,5QMM	RST20i3/2 crimp contact, female, 20A, for cross section 2.5 mm²/AWG14
02.122.9300.0	female contact CRIMP RST20i2/i3 4,0QMM	RST20i3/2 crimp contact, female, 20A, for cross section 4.0 mm²/AWG12

assembly

item no.	type	description
96.233.1030.0	cable assembly RST20i3K1BS 25 10GL	RST® CLASSIC connecting cable, female - male, number of poles 3, rated voltage 250 V, rated current 20 A, cable type H07RN-F, fire class Eca, total length 1 m, nominal cross section conductor 2.5 mm², color of coding/ contact carrier light grey
96.136.2153.0	device connector RST20i3C S1 M13V GL	RST® CLASSIC device connector, modular, angled 7°, M16, number of poles 3, model male, connection type crimp, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier light grey
96.132.2153.0	device connector RST20i3C S1 M03V GL	RST® CLASSIC device connector, modular, straight, M16, number of poles 3, model male, connection type crimp, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier light grey
96.134.2053.0	device connector RST20i3C S1 M90V GL	RST® CLASSIC device connector, modular, angled 90°, M20, number of poles 3, model male, connection type crimp, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier light grey
96.132.2053.0	device connector RST20i3C S1 M00V GL	RST® CLASSIC device connector, modular, straight, M20, number of poles 3, model male, connection type crimp, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier light grey

