

product data sheet

item no. G5.536.0103.1

distributor MST32I3V 2P1S25 01 BLC1

METALYNX² T-distributor, with mounting option, SPUR (tap off fused with 10 A), number of poles 3, rated voltage 250 V, rated current 32 A, number of inputs 1, number of outputs 2, color of coding/ contact carrier blue

item no.	G5.536.0103.1
EAN	4049088220173
order unit	25 piece(s)

certificates / approvals

technical data

general

rated current	32 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 1
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	blue
Pole codification	L, N, PE

lead

model	spur
microfuse (6,3x25 mm)	10 A
drop	sheathed cable LSOH
no. of poles on drop	3
cross section of drop	2.5 mm ²
termination of drop	free end
length of drop	1 m
length of open end	1 m
stripping length of drop	10 mm
design of conductor ends	ultrasonically compressed wire ends
color of the coding pin	sky blue (C1)
wiring system	
internal cross section	

model

number of inputs	1
number of outputs	2
type of fastening	yes
degree of protection (IP)	IP20
type of distributor	spur

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.721 kWh/St
insulation components continuous temperature	100 °C

surface finish	silver-plated
----------------	---------------