

product data sheet

item no. G5.966.2042.6

distributor MST20I6V 2P1M15 20 GRC6

METALYNX² T-distributor, parallel connection, with fastening option, number of poles 6, rated voltage 250 V, rated current 20 A, number of inputs 1, number of outputs 2, color of coding/ contact carrier grey

item no.	G5.966.2042.6
EAN	4049088280948
order unit	15 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 6
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	grey
Pole codification	1, 2, 3, 4, N, PE

lead

model	T-distributor
microfuse (6,3x25 mm)	
drop	sheathed cable LSOH
no. of poles on drop	6
cross section of drop	1.5 mm ²
termination of drop	free end
length of drop	2 m
length of open end	2 m
stripping length of drop	10 mm
design of conductor ends	
color of the coding pin	grey (C6)
wiring system	
internal cross section	

model

number of inputs	1
number of outputs	2
type of fastening	yes
degree of protection (IP)	IP20
type of distributor	T-distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.918 kWh/St
insulation components continuous temperature	100 °C

surface finish	silver-plated
----------------	---------------