

product data sheet

item no. G5.956.5042.5

distributor MST20I6V 2P1M15 50 PBC5

METALYNX² T-distributor, with mounting option, Conduit Drop,
number of poles 5, rated voltage 250 V / 400 V, rated current 20 A,
number of inputs 1, number of outputs 2, color of coding/ contact
carrier pastel blue

item no.	G5.956.5042.5
EAN	4049088280917
order unit	8 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 5
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	pastel blue
Pole codification	1, 3, 4, N, PE
RAL number coding/contact insert	5024

lead

model	T-distributor
microfuse (6,3x25 mm)	
drop	sheathed cable LSOH
no. of poles on drop	5
cross section of drop	1.5 mm ²
termination of drop	free end
length of drop	5 m
length of open end	5 m
stripping length of drop	10 mm
design of conductor ends	ultrasonically compressed wire ends
color of the coding pin	pastel blue (C5)
wiring system	
internal cross section	

model

number of inputs	1
number of outputs	2
type of fastening	yes
degree of protection (IP)	IP20
type of distributor	T-distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	3.448 kWh/St

insulation components continuous temperature	100 °C
surface finish	silver-plated