

product data sheet

item no. G5.451.0203.0

cable assembly MST20i5KC-S 25 020BRC0

METALYNX² connection cable, male - free end, number of poles 5,
rated voltage 250 V, rated current 20 A, cable type metal conduit
16 mm, fire class Eca, total length 2 m, nominal cross section
conductor 2.5 mm², color of coding/ contact carrier brown

item no.	G5.451.0203.0
EAN	4049088277818
order unit	15 piece(s)

certificates / approvals



technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 0
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	brown
Pole codification	1, 2, 3, 4, 5
color of housing inclusive strain relief	black

lead

model	metal conduit 16 mm
inner cores	single cores LSOH
single cores	H07Z-R
color of the coding pin	brown (C0)

model

nominal cross section conductor	2.5 mm ²
degree of protection (IP)	IP20
wire strip length	10 mm
sheath strip length	200 mm
preparation of conductor ends	tin-plated
cable type	metal conduit 16 mm
version of cable	male - free end
type of cord set	connection cable
version cable end 1	free end
version cable end 2	MST20i5 plug

dimensions

total length	2 m
--------------	-----