

product data sheet

item no. G5.451.0503.5

cable assembly MST20i5KC-S 25 050PBC5

METALYNX² connection cable, male - free end, number of poles 5,
rated voltage 250 V / 400 V, rated current 20 A, cable type metal
conduit 16 mm, fire class Eca, total length 5 m, nominal cross
section conductor 2.5 mm², color of coding/ contact carrier pastel
blue

item no.	G5.451.0503.5
EAN	4049088207594
order unit	5 piece(s)

certificates / approvals



technical data

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 5
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	pastel blue
Pole codification	1, 3, 4, N, PE
color of housing inclusive strain relief	black

lead

model	metal conduit 16 mm
inner cores	single cores LSOH
single cores	H07Z-R
color of the coding pin	pastel blue (C5)

model

nominal cross section conductor	2.5 mm ²
degree of protection (IP)	IP20
wire strip length	10 mm
sheath strip length	200 mm
preparation of conductor ends	tin-plated
cable type	metal conduit 16 mm
version of cable	male - free end
type of cord set	connection cable
version cable end 1	free end
version cable end 2	MST20i5 plug

dimensions

total length	5 m
--------------	-----