

## product data sheet

item no. G5.441.1004.4

### cable assembly MST20i4KC-S 40 100TRC4

METALYNX<sup>2</sup> connection cable, male - free end, number of poles 4,  
rated voltage 250 V / 400 V, rated current 20 A, cable type metal  
conduit 16 mm, fire class Eca, total length 10 m, nominal cross  
section conductor 4 mm<sup>2</sup>, color of coding/ contact carrier red

|            |               |
|------------|---------------|
| item no.   | G5.441.1004.4 |
| EAN        | 4049088257599 |
| order unit | 4 piece(s)    |

### certificates / approvals



### technical data

#### general

|                                          |                                  |
|------------------------------------------|----------------------------------|
| rated current                            | 20 A                             |
| rated voltage                            | 250 V / 400 V                    |
| rated impulse voltage                    | 4 kV                             |
| pollution degree                         | 2                                |
| mechanical coding                        | code 4                           |
| lockable                                 | self-locking (unlocking by tool) |
| color of coding/ contact carrier         | red                              |
| Pole codification                        | 2, N, PE, 1                      |
| color of housing inclusive strain relief | black                            |

#### lead

|                         |                     |
|-------------------------|---------------------|
| model                   | metal conduit 16 mm |
| inner cores             | single cores LSOH   |
| single cores            | H07Z-R              |
| color of the coding pin | red (C4)            |

#### model

|                                 |                     |
|---------------------------------|---------------------|
| nominal cross section conductor | 4 mm <sup>2</sup>   |
| degree of protection (IP)       | IP20                |
| wire strip length               | 10 mm               |
| sheath strip length             | 200 mm              |
| preparation of conductor ends   | tin-plated          |
| cable type                      | metal conduit 16 mm |
| version of cable                | male - free end     |
| type of cord set                | connection cable    |
| version cable end 1             | free end            |
| version cable end 2             | MST20i4 plug        |

#### dimensions

|              |      |
|--------------|------|
| total length | 10 m |
|--------------|------|