

product data sheet

item no. G5.352.0203.7

cable assembly MST20i5KCB- 25P 020GEC7

METALYNX² connection cable, female - free end, number of poles
5, rated voltage 250 V / 400 V, rated current 20 A, cable type
H05VV-F, fire class Eca, total length 2 m, nominal cross section
conductor 2.5 mm², color of coding/ contact carrier yellow

item no.	G5.352.0203.7
EAN	4049088245695
order unit	15 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 7
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	yellow
Pole codification	3, N, PE, 2, 1
color of housing inclusive strain relief	black

lead

model	sheathed cable PVC
single cores	
color of the coding pin	yellow (C7)

model

nominal cross section conductor	2.5 mm ²
degree of protection (IP)	IP20
wire strip length	9 mm
sheath strip length	100 mm
preparation of conductor ends	ultrasonically compressed wire ends
cable type	H05VV-F
cable color	black
version of cable	female - free end
type of cord set	connection cable
version cable end 1	MST20i5 female
version cable end 2	free end

dimensions

total length	2 m
--------------	-----