

## product data sheet

item no. G5.352.0103.7

cable assembly MST20i5KCB- 25P 010GEC7

METALYNX<sup>2</sup> connection cable, female - free end, number of poles  
5, rated voltage 250 V / 400 V, rated current 20 A, cable type  
H05VV-F, fire class Eca, total length 1 m, nominal cross section  
conductor 2.5 mm<sup>2</sup>, color of coding/ contact carrier yellow

|            |               |
|------------|---------------|
| item no.   | G5.352.0103.7 |
| EAN        | 4049088247606 |
| order unit | 30 piece(s)   |

## certificates / approvals

## technical data

### general

|                                          |                                  |
|------------------------------------------|----------------------------------|
| rated current                            | 20 A                             |
| rated voltage                            | 250 V / 400 V                    |
| rated impulse voltage                    | 4 kV                             |
| pollution degree                         | 2                                |
| mechanical coding                        | code 7                           |
| lockable                                 | self-locking (unlocking by tool) |
| color of coding/ contact carrier         | yellow                           |
| Pole codification                        | 3, N, PE, 2, 1                   |
| color of housing inclusive strain relief | black                            |

### lead

|                         |                    |
|-------------------------|--------------------|
| model                   | sheathed cable PVC |
| single cores            |                    |
| color of the coding pin | yellow (C7)        |

### model

|                                 |                                     |
|---------------------------------|-------------------------------------|
| nominal cross section conductor | 2.5 mm <sup>2</sup>                 |
| degree of protection (IP)       | IP20                                |
| wire strip length               | 9 mm                                |
| sheath strip length             | 100 mm                              |
| preparation of conductor ends   | ultrasonically compressed wire ends |
| cable type                      | H05VV-F                             |
| cable color                     | black                               |
| version of cable                | female - free end                   |
| type of cord set                | connection cable                    |
| version cable end 1             | MST20i5 female                      |
| version cable end 2             | free end                            |

### dimensions

|              |     |
|--------------|-----|
| total length | 1 m |
|--------------|-----|