

product data sheet

item no. G5.341.0704.2

cable assembly MST20I4KCB- 40 070TBC2

METALYNX² connection cable, female - free end, number of poles
4, rated voltage 250 V, rated current 25 A, cable type metal conduit
16 mm, fire class Eca, total length 7 m, nominal cross section
conductor 4 mm², color of coding/ contact carrier turquoise blue

item no.	G5.341.0704.2
EAN	4049088219016
order unit	5 piece(s)

certificates / approvals

technical data

general

rated current	25 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 2
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	turquoise blue
Pole codification	2, N, PE, 1
color of housing inclusive strain relief	black

lead

model	metal conduit 16 mm
inner cores	single cores LSOH
single cores	H07Z-R
color of the coding pin	turquoise blue (C2)

model

nominal cross section conductor	4 mm ²
degree of protection (IP)	IP20
wire strip length	10 mm
sheath strip length	800 mm
preparation of conductor ends	tin-plated
cable type	metal conduit 16 mm
version of cable	female - free end
type of cord set	connection cable
version cable end 1	MST25i4 female
version cable end 2	free end

dimensions

total length	7 m
--------------	-----