



产品认证证书

证书编号: CQC17003177248

申请人名称及地址

Wieland Electric GmbH
Brennerstrasse 10-14 D-96052 Bamberg Germany

制造商名称及地址

Wieland Electric GmbH
Brennerstrasse 10-14 D-96052 Bamberg Germany

生产企业名称及地址

Wieland Electric s.r.o. (V026734)
Nadrazni 1557, 35601 Sokolov Czech Republic

产品名称和系列、规格、型号

电连接器

见附件

产品标准和技术要求

GB/T34989-2017

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-462222-2011 认证规则的要求, 特发此证。

发证日期: 2019 年 04 月 23 日

本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2017 年 09 月 18 日

主任: _____

陆楠



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

C 0144776



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC17003177248

NAME AND ADDRESS OF THE APPLICANT

Wieland Electric GmbH
Brennerstrasse 10-14 D-96052 Bamberg Germany

NAME AND ADDRESS OF THE MANUFACTURER

Wieland Electric GmbH
Brennerstrasse 10-14 D-96052 Bamberg Germany

NAME AND ADDRESS OF THE FACTORY

Wieland Electric s.r.o. (V026734)
Nadrazni 1557, 35601 Sokolov Czech Republic

PRODUCT NAME, MODEL AND SPECIFICATION

Electrical Connector
See Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T34989-2017

TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462222-2011 .

Valid from: Apr.23,2019

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

Date of original issued: Sep.18,2017

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0144776



产品认证证书

附 录

第 1 页 共 3 页

证书编号: CQC17003177248

纸 号: 144776

系列命名规则:

RST 20i 系列

20A 250/400V 无分断能力 2、3、4、5 极 IP66/68 不带联锁 无负载
5000 次操作循环 40T100 污染等级 3 过电压保护类别 III 灼热丝 850℃
针焰 30s 球压 125℃ PTI400

系列命名如下:

RST 20i 3 S B13 Z R1 V SW

(1) (2) (3) (4) (5) (6) (7) (8)

1	系列	RST20i	RST20i
2	芯数	2	2 芯
		3	3 芯
		4	4 芯
		5	5 芯
3	连接方式	S	螺纹夹紧
		F	无螺纹夹紧
4	插针类型	B	母头, 13/23/1/2 仅表示序号, 无含义
		S	公头, 13/23/1/2 仅表示序号, 无含义
5	固定方式及出线方向	Z	线端水平出线
		Y	线端 90 度垂直出线
		M0	板端水平出线

注: 此附录与证书同时使用时有效。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 2 页 共 3 页

证书编号: CQC17003177248

纸 号: 144776

		M1	板端 7 度出线
		M2	板端 20 度出线
		M9	板端 90 度垂直出线
6	线缆直径/安装孔径	R1	6-10mm
		R2	10-14mm
		R3	13-18mm
		RW	矩形电缆
		RXS	2 个电缆入口, AS-i
		RX	2 个电缆入口, 6-10mm
		RY	2 个电缆入口, 10-14mm
		0	M20(即 PG11;PG13.5;PG16)
		1	M25(即 PG21)
		2	M32(即 PG29)
		3	M16(即 PG20)
		ASS	AS-i 总线
7	锁定	V	带有锁定
		空白	没有卡扣
		L	AS-i
8	插芯颜色	GL	浅灰色
		SW	黑色
		BR0	棕色
		KG0	灰色
		GN0	绿色
		BL0	淡蓝色
		TB0	蓝绿色

注: 此附录与证书同时使用时有效。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

证书编号: CQC17003177248

第 3 页 共 3 页

纸 号: 144776

		GE	黄色
--	--	----	----

注: 此附录与证书同时使用时有效。

主任:

陆杨



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>